

Slabber

Mfg: **Not Specified**

Model:

Stock No: **SMBS243.1**

Serial No:

Slabber. Aperture/clearance: 1 ft. 2 in. W x 3-5/8 in. H. Conveyor belt dimensions: 10 in. W x 4 ft. 2 in. L. Infeed/exit height: 3 ft. 5 in. This machine will make slabs of a block of meat, cheese, or other bulk block item. Minimum slab thickness: 1/2 in. Maximum slab thickness: 1-3/4 in. Emerson Motor, 1/2 hp, 1725 rpm, 115/230 V, 9.2/4.6 amps, 60 Hz, 3 phase, (blade drive). Baldor electric motor, 1/2 hp, 1725 rpm, 115/230 V, 7.4/3.7 amps, 60 Hz, 3 phase, (conveyor drive). Gear reducer ratio: 20, 86 rpm (final). Overall dimensions: 4 ft. 4 in. L x 2 ft. 10 in. W x 4 ft. 8 in. H.





EMERSON MOTOR DIVISION ST. LOUIS, MO. U.S.A. SPECIAL SERVICE DUTY

MODEL C63CXSGB-3719 CAT. 1661

H.P. 1/2 R.P.M. 1725 S.F. 1.0

V. 115/230 HZ 60 PH 1 CODE M

A. 9.2/4.5 S.F.A. AMB 40 C

TIME RATING CONT. INSUL. CLASS A

THERMALLY PROTECTED

CONTINUOUS DUTY - REGR. EVERY YEAR
 INTERMITTENT DUTY - REGR. EVERY 2 YEARS
 OCCASIONAL DUTY - REGR. EVERY 5 YEARS
 REGR. EACH BEARING WITH 30/35 DROPS

CONNECTIONS
 LOW VOLTAGE HIGH VOLTAGE

TO REVERSE ROTATION SWITCH RED & BLK LEADS

EM J22922 MFG. NO. MB04C ASSEMBLED IN MEXICO

WARNING: MOTOR MUST BE PROPERLY GROUNDED AND TERMINAL COVER MUST BE IN PLACE TO REDUCE POTENTIAL ELECTRICAL SHOCK.



