

## Goulds Centrifugal Pump

**Mfg: Goulds**

**Model: 3196**

**Stock No: SMBV001**

**Serial No: 764C237.2**

Goulds Centrifugal Pump. Model: 3196. S/N: 764C237.2. Capacity: 70 gpm @ 140 tdh (~61 psi using specific gravity of water = 1). Displacement per Revolution: 0.02 gal. Century Motor, 5 hp, 3500 rpm, 230/460 V, 13.4/6.7 amps, 60 Hz, 3 phase. 6 in. cavity for impeller. 5 in. impeller diameter. This pump has a fully open impeller, external impeller adjuster, and back pull-out design. Can be used in chemical, petrochemical, pulp, paper, primary metals, food & beverage. Inlets: (1) 1 ½ in. dia. port with a 5 in. flange and (4) ½ in. bolt holes. Outlets: 1 in. dia. port with a 4 ½ in. flange and (4) ½ in. bolt holes. Overall dimensions: 3 ft. 7 in. L x 1ft. 2 in. W x 1 ft. 10 in. H.



