

Osgood Cup Filler

Mfg: Osgood

Model: 3503

Stock No. SKFC064.68

Serial No. 3503-1

Osgood Cup Filler. Model: 3503. S/N 3503-1. Cup size: 5-1/2 in. dia. Mold width: 17 in. (6) 1 in. dia. fill valves. Chute width (lid): 6-1/2 in. Lid press: 6 in. dia. Baldor Industrial Motor, 5 hp, 1725 rpm, 206-230/460 V, 15-13.2/6.6 amps, 60 Hz, 3 phase. Lid Roller Baldor Industrial Motor, 1/3 hp, 208-230/460 V, 2.1-2/1 A, 60 Hz, 3 phase. The Osgood Super-Duty filler features a mechanical cam drive and weldment base. It is the benchmark for ruggedness and sanitation. Its super-fast design is state of the art, with a low profile and patented servo drives. Conveyor infeed height: 43 in. Conveyor exit height: 42 in. Inlets: (2) 3 in. dia. I-line fittings (female). Overall dimensions: 18 ft. 6 in. L x 45 in. W x 75 in. H.





