

Conveyor Section with Reject Mechanism

Mfg:

Model:

Stock No. SNBB249.

Serial No.

Conveyor Section with Reject Mechanism. Belt dimensions: 48 in. L x 12 in. W. Reject mechanism pneumatically operated; (2) sensors. Baldor motor: 5 hp, 1,725 rpm, 208-230/460 V, 1.9/9 amps, 60 Hz, 3 phase. Ideal for placement immediately after metal detectors and checkweighers for defective product ejection. Overall dimensions: 4 ft. L x 4 ft. 10 in. W x 2 ft. 9 in. H.



