

Tri-Flow C114 Centrifugal Pump

Mfg: Tri-Flow

Model: C114MD56T-S

Stock No. SNSL366.

Serial No. V2247

Tri-Flow C114 Centrifugal Pump. Model: C114MD56T-S. S/N: V2247. Pump capacity: 135 gpm. External balanced seal. Impeller: 2-3/4 in. diameter. Baldor Industrial motor, 1 hp, 3450 rpm, 230/460 V, 3.2/1.5 amps, 60 Hz, 3 phase. Typical applications: dairy products, cream style corn, tomatoes, beverages, etc. Also applicable for acid cleaning solutions and detergents. Pump inlet/outlet: 1-1/2 in. $\frac{1}{2}$ sqline. Overall dimensions: 18 in. L x 9 in. W x 7 in. H.



