

Waukesha Cherry-Burrell 220 Positive Displacement Pump

Mfg: Waukesha

Model: 220

Stock No. SNCC091.33

Serial No. 131949

Waukesha Cherry-Burrell 220 Positive Displacement Pump. Model 220. S/N: 131949. Pumping capacity: 132.5 gpm. Nominal capacity: 310 gpm. Displacement per revolution: 0.522 gal/rev. Maximum allowable speed: 600 rpm. Seal option: double mechanic seal with water flush. Inverter Drive Motor, 15 hp, rpm, 460 V, 60 Hz, 3 phase. Baldor Industrial Motor, 1/3 hp, 3450 rpm, 115/208-230 V, 2.5/1.3-1.25 amps, 60 Hz, 3 phase. Sew-Eurodrive Speed Reducer, ratio: 13.01, 265 rpm (final). Typical applications include: bakery, beverage, canning, confectionary, cosmetics, dairy, meat packaging, and pharmaceutical. 316 stainless steel standard construction. 3-A sanitary rated. Inlets/outlets: (2) 4 in. dia S-line fittings. Overall dimensions: 82 in. L x 18-1/2 in. W x 32 in. H.



