

Fristam FP-Series Centrifugal Pump

Mfg: Fristam

Model: FP722A

Stock No. SNCC180.4a

Serial No. 221-29327

Fristam FP-Series Centrifugal Pump. Model: FP722A. S/N: 221-29327. Capacity: approx. 62 gpm @ 10.5 psi and 24 tdh. Impeller diameter: 6 in. Seal option: single mechanical. Motor: 2 hp, 1800 rpm, 460 V, 3 amps, 3 phase. The heavy-duty, high performance sanitary centrifugal pumps handle the most demanding applications such as vacuum withdrawal from evaporators, viscous, hot, or abrasive products. 316L Stainless steel construction. Inlets: (1) 1-1/2 in. S-Line. Outlets: (1) 1-1/2 in. S-Line. Overall dimensions: 25 in. L x 8 in. W x 15-1/2 H.



