

WHE 1/3 Jacketed Stainless Steel Batch Tank – 2000 Gallons

Mfg: WHE Process Systems

Model:

Stock No: SPGT037.80

Serial No:

WHE 1/3 Jacketed Stainless Steel Batch Tank. Approximate capacity: 2000 gallons. Inside dimensions: 83 in. dia. x 84 in. side wall. Tank comes equipped with upper and lower agitators, dual spray balls, (4) Vishay – Nobel, model KIS-30KN (6744 lbs. rating) load cells, and an internal access ladder. Bottom agitator dimensions (approx.): 6 ft. 2 in. L x 1 ft. W. Upper agitator dimensions: 2 ft. 1 in. L x 4 in. W. Reliance Electric Motor, 5-2.5 hp, 1725/860 rpm, 575/575 V, 5.44/4.32 amps, 60 Hz, 3 phase. Final rpm: 48/24. Inlets/Outlets (product): (1) 4 in. diameter S-Line fitting, (1) 3 in. diameter S-Line fitting, (1) 1 ft. 6 in. diameter manhole with lid, (1) 3 in. diameter S-Line fitting. Inlets/Outlets (media): (1) 1 in. diameter MNPT, (1) 1 in. diameter FNPT. Overall dimensions: 8 ft. L x 7 ft. 10 in. W x 13 ft. 4 in. H.





