

Tri-Flow C114 Centrifugal Pump

Mfg: Tri-Flow

Model: C114MD56T-S

Stock No. SNSL365.

Serial No. V2240

Tri-Flow C114 Centrifugal Pump. Model: C114MD56T-S. S/N: V2240. Pump capacity: 65 gpm. External balanced seal. Impeller: 3-1/2 in. diameter. Reliance Electric Motor, 1/2 hp, 1725 rpm, 2-2/1 amps, 60 Hz, 3 phase. Typical applications: dairy products, cream style corn, tomatoes, beverages, etc. Also applicable for acid cleaning solutions and detergents. Pump inlet/outlet: 1-1/2 in. 'S' line. Overall dimensions: 17 in. L x 10 in. W x 7 in. H.

