

Tri Clover C216 Centrifugal Pump

Mfg: Tri Clover

Model: C216TD18T-S

Stock No. SPPP820.4a

Serial No. M7922

Tri Clover C216 Centrifugal Pump. Model: C216TD18T-S. S/N: M7922. Capacity: 65 gpm @ 6.2 psi and 16 tdh. Impeller diameter: 4-1/2 in. Lincoln Motor, 3 hp, 1750 rpm, 230/460 V, 8.4/4.2 amps, 60 Hz, 3 phase. C-Series centrifugal pumps are engineered to deliver dependable performance and easy maintenance in virtually any low-viscosity application. Serving the following industries: pharmaceutical, biotechnology, fine chemical, food, beverage, and dairy industries. Inlets: (1) 2 in. dia. threaded fitting. Outlets: (1) 1-1/2 in. dia. threaded fitting. Overall dimensions: 20-1/2 in. L x 12 in. W x 10-1/2 in. H.



