

## 1993 Goring Kerr Metal Detector

**Mfg: Goring Kerr**

**Model: Tek 21**

**Stock No: SPPF295.16**

**Serial No: 48334**

1993 Goring Kerr Metal Detector. Model: Tek 21. S/N: 48334. Sensor capacities: 1mm ferrous, 1.5 mm non-ferrous, 3 mm stainless steel. Maximum aperture/clearance above belt without applied load: 38 in. W x 1 in. H. Maximum aperture/clearance above belt with applied load: 38 in. W x 3-3/4 in. H. Features pneumatic reject device. Electrical requirements: 110 V, 50/60 Hz. Baldor Industrial Motor: 1 hp, 1,725 rpm, 208-230/460 V, 60 Hz, 3 phase. Hub City Motor Drive: 1/1 ratio. Overall dimensions: 5ft. 10 in. L x 4ft. 9 in. W x 3ft. 8 in. H.





**BALDOR**  
INDUSTRIAL MOTOR  
THREE PHASE

CAT. NO.			CONNECTION
SPEC.			WINDING
FRAME	56C	SER. 1388	VOLTS
H.P.	1		LINE
VOLTS	208-230/460		HIGH VOLTAGE
	3.6-3.4/1.7		LINE
R.P.M.	1725		
HZ.	60	PH. 3 CLASS	
SER. F.	4.75	DES. 7 CODE J	
FULL LOAD EFF.	77.3	P.F. 74%	
RATING	400 AMB-GONT 5		

BALDOR ELECTRIC CO.  
FT. SMITH, ARK.  
MFD. IN U.S.A.

NP0025