

Bottle Conveyor

Mfg:

Model:

Stock No. SUBF255.1a

Serial No.

Bottle Conveyor. 2-Piece conveyor with maximum aperture/clearance above belt of 4-1/2 in. W x 10 in. H. Flip-top covers. Part #1: Sew-Eurodrive motor, 3/4 hp, 1700 rpm, 230/460 V, 3.05/1.53 amps, 60 Hz, 3 phase. Sew-Eurodrive Speed Reducer, ratio: 15.74, 108 rpm (final). Part #2: Sew-Eurodrive Motor, 1 hp, 1700 rpm, 230/460 V, 3.9/1.93 amps, 60 Hz, 3 phase, 60 Hz. Sew-Eurodrive Speed Reducer, ratio: 15.84, 107 rpm (final). Conveyor infeed/exit height: 27 in. Overall dimensions: 118 in. L x 27 in. W x 38 in. H.

