

Stainless Steel Cooling Tunnel with Spray System

Mfg:

Model:

Stock No. WFAF001.

Serial No.:

Stainless Steel Cooling Tunnel with Spray System. Product aperture/clearance: 8 ft. 1 in. W x 18-1/2 in. H. Infeed Conveyor uses (2) belts. Maximum product width: 5-1/2 in. W. Drive sprocket size: 6 in. dia. x 1 in. W with a 3/4 in. tooth pitch. Baldor Motor, 2 hp, 1725 rpm, 208-230/460 V, 6.5-6.2/3.1 amps, 60 Hz, 3 phase. Exit Conveyor maximum product width: 7-1/2 in. W. Drive sprocket: 6 in. dia. x 1/2 in. W with a 3/4 in. tooth pitch. Baldor Motor, 2 hp, 1740 rpm, 208-230/460 V, 6-6.5/2.8 amps, 60 Hz, 3 phase. Baldor Motor 2, 1/2 hp, 1725 rpm, 208-230/460 V, 1.8-1.6/.6 amps, 60 Hz, 3 phase. Baldor Gear Reducer, ratio: 30, 57.5 rpm (final). (3) Liquid Return Tanks- 40 Gallon, inlet: 2 in. dia. S-Line, outlet: 4 in. dia. S-Line. (2) Waukesha 200 Series Heavy-Duty Sanitary Centrifugal Pumps, Model: U2105, S/N: 125458. Maximum pumping capacity: 1400 gpm @ 133 tdh. Baldor Motor, 15/20 hp, 1760 rpm, 230/460 V. 26, 38/19 amps, 60 Hz, 3 phase. Leeson Motor, 1/3 hp, 1725/1425 rpm, 690 rpm (final), 208-230/460 V, 1.3/1.2 amps, 60/50 Hz. 3 phase. Inlets/outlets: (1) 4 in. dia. S-Line port. Overall dimensions: 45 ft. 6 in. L x 12 ft. 3 in. W x 75 in. H.









