

Gem Line Stainless Steel Blancher- 2.0 cu. ft.

Mfg:

Model:

Stock No. SSLP084.6

Serial No. 531B69 Blancher

Gem Line Stainless Steel Blancher- 2.0 cu. ft. S/N: 531B69 Blancher. Screw auger dimensions: 12 in. dia. x 95 in. L. Auger housing diameter: 12-1/2 in. Blancher is equipped with a 91 in. L manifold, with (13) valves, that supplies liquid for product cleansing; each valve feeds bottom sprayers. Liquid is drained by a tubular screen: Tyler sieve: 3 mesh (.25 in). Product is cleansed of liquid after passing through a rotating pick-up basket. Sump tank has a capacity of 10 gallons (1.3 cu. ft). Falk Shaft Mounted Motor Drive, 19.41 ratio. Inlets: (1) 1 in. dia. NPT (liquid, female), (1) 12 in. L x 8 in. W product infeed. Outlets: (1) 2 in. dia. pipe, (1) 8-1/2 in. W x 3-1/2 in. H discharge chute. Overall dimensions: 11 ft 7 in. L x 39 in. W x 46 in. H.

Additional features include: (4) casters for easy positioning, (1) thermometer, (1) temperature probe.







