

Wash Tunnel Conveyor

Mfg: not specified

Model: -

Stock No.: **TAPG40.5a**

Serial No.: -

Wash Tunnel Conveyor. Belt width: 12 in. Maximum aperture/clearance above belt: 6 in. W x 11 in. H. Height at conveyor infeed/exit: 32 in. U.S. Electric Motor, 1/2 hp, 1725 rpm, 40 amps, 60 Hz, 3 phase. Drive, 19.4 ratio, 19 rpm (final). Inlets: (1) 1 in. dia NPT (female). (4) Height adjustable legs. Overall dimensions: 12 ft. 9 in. L x 27 in. W x 50-1/2 in. H.





