



GIAFLEX

www.alfalaval.si

Alfa Laval in brief

Alfa Laval is a leading global provider of specialized products and engineered solutions.

Our equipment, systems and services are dedicated to helping customers to optimize the performance of their processes. Time and time again.

We help our customers to heat, cool, separate and transport products such as oil, water, chemicals, beverages, foodstuffs, starch and pharmaceuticals.

Our worldwide organization works closely with customers in almost 100 countries to help them stay ahead.

How to contact Alfa Laval

Up-to-date Alfa Laval contact details for all countries are always available on our website at www.alfalaval.com

Alfa Laval reserves the right to change specifications without prior notification.

© 2008 Alfa Laval

ECF00149EN 1009

GIAFLEX

GIA-S d.o.o., Industrijska cesta 5, 1290 Grosuplje, Slovenija
Telefon: +386 1 7865 300, Telefax: +386 1 7863 568,
info@gia.si, www.giaflex.com

Brazed plate heat exchangers

The product range of the world's leading supplier



ALFA LAVAL is a trademark registered and owned by Alfa Laval Corporate AB

Technical specifications

Brazed plate heat exchanger (BHE) data and dimensions

| | CB14 | CBH16 | CBH18 | CB20 | CB30 | CB52 | CB60 | CB76 | CB77 | CB100 (CBH100) | CB200 (CBH200) | CB300 | CB400 |
|--|------------------|-------------------|-------------------|------------------|-----------------|------------------|------------------|-------------------------------|-----------------|-----------------|---------------------------------|-----------------|-----------------|
| Channel type | H | A, H | H | H | H, M, L | L, M | H | H, E, A, M, L | H, L, M | M | H, L, M | H, L, M | H, L |
| Max./min. design temperature (°C) | 175/-160 | 225/-50 | 225/-50 | 175/-160 | 175/-160 | 175/-160 | 175/-160 | 175/-160 | 175/-160 | 175/-160 | 175/-160 | 175/-160 | 150/-160 |
| Max. design pressure (S3-S4/S1-S2) (bar) * | 32/32 | 30/30 | 25/25 | 16/16 | 32/32 | 32/32 | 32/32 | 32/32 ¹⁾ | 27/16 | 20/20 (25/25) | 16/16 (25/25) | 27/16 | 32/27 |
| Volume/channel (S3-S4/S1-S2) (litres) | 0.02 | 0.024 (H) | 0.039 | 0.028 | 0.054 | 0.095 | 0.103 | 0.25 ^{2)/} 0.25 | 0.25 | 0.2 | 0.51 | 0.58/0.69 | 0.74 |
| Max. flowrate (S3-S4/S1-S2) (m ³ /h) ** | 3.6 | 3.6 | 3.6 | 7.6 | 12.5/7.6 | 7.6/12.7 | 12.5/7.6 | 34 | 34/63 | 63 | 97 | 70/160 | 170 |
| Height, a (mm) | 207 | 211 | 316 | 324 | 313 | 526 | 527 | 618 | 618 | 491 | 742 | 990 | 990 |
| Width, b (mm) | 77 | 75 | 75 | 94 | 113 | 111 | 113 | 191 | 191 | 250 | 324 | 366 | 390 |
| Vertical connection distance, c (mm) | 172 | 172 | 278 | 270 | 250 | 466 | 466 | 519 | 519 | 378 | 622 | 816/861 | 825 |
| Horizontal connection distance, d (mm) | 42 | 40 | 40 | 46 | 50 | 50 | 50 | 92 | 92 | 138 | 205 | 213.5 | 225 |
| Plate pack length, A (mm) | (n x 2.35) + 8 | (n x 2.16) + 8 | (n x 2.2) + 6.5 | (n x 1.5) + 8 | (n x 2.35) + 9 | (n x 2.4) + 10 | (n x 2.35) + 13 | (n x 2.85) + 10 ³⁾ | (n x 2.85) + 10 | (n x 2.2) + 12 | (n x 2.7) + 11 / (n x 2.7) + 14 | (n x 2.65) + 11 | (n x 2.56) + 14 |
| Weight empty (kg) *** | (n x 0.06) + 0.7 | (n x 0.04) + 0.27 | (n x 0.065) + 0.4 | (n x 0.08) + 0.9 | (n x 0.1) + 1.2 | (n x 0.23) + 1.9 | (n x 0.18) + 2.1 | (n x 0.44) + 7 | (n x 0.44) + 7 | (n x 0.38) + 13 | (n x 0.6) + 29 / (n x 0.6) + 32 | (n x 1.26) + 40 | (n x 1.35) + 62 |
| Standard connection, external thread (in) | 3/4" | 3/4" | 3/4" | 1" | 1 1/4" / 1" | 1 1/4"/1" | 1 1/4" / 1" | 2" | 3" weld/2" | ISO G2"/2 1/2" | 3" | 4"/2 1/2" | 4" |
| Plate material | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 |
| Connection material | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 | AISI 316 |
| Brazing material | Copper | Copper | Copper | Copper | Copper | Copper | Copper | Copper | Copper | Copper | Copper | Copper | Copper |
| Max. number of plates | 50 | 50 | 50 | 110 | 150 | 150 | 150 | 190 | 190 | 270 | 230 | 250 | 270 |
| Radiator heating, capacity (kW) ⁴⁾ | 90 | 110 | 130 | 170 | 430 | 500 | 500 | 1200 | 1800 | 2000 | 2900 | 3200 | 4500 |
| Tap water heating, capacity (kW) ⁴⁾ | 60 | 70 | 80 | 140 | 200 | 380 | 400 | 700 | 900 | 1300 | 2100 | 2900 | 3500 |

*) According to PED **) Water at 5 m/s (connection velocity) ***) excluding connections n = number of plates

1) M and L channels 28/27 bar 2) E channel 0.18/0.18; A channel 0.18/0.25 3) A channels (n x 2.5) + 10, E channels (n x 2.2) + 10 4) Varies from country to country depending on temperature duty. Given values for typical district heating installations.

An identical message, globally

By intense listening to market demands, Alfa Laval has reached a position of global leadership within the segment brazed plate heat exchangers (BHEs). Our experience is longstanding and worldwide, and it is reflected in the function of our products. Alfa Laval technology brings customers all over the world an identical message: second best should never be an alternative!

A wide range of applications

BHEs offer multiple benefits. The brazing technology eliminates the need for seals and thick frame plates. A copper film covering


the contact surface melts and connects the stainless steel plates while the heat will be transferred via the melting points. The basic BHE design – refined over the years by Alfa Laval – offers excellent resistance to pressure and thermal fatigue in a wide range of heating and cooling applications. For reasons of reliability and cost-efficiency, BHEs from Alfa Laval are frequently a natural first alternative all over the world.

A variety of design options

For every application there is an optimal solution. This brochure shows heat ex-

changers suitable for HVAC applications. The design options are multiple. A number of plate patterns for each plate size means optimal function for any application. The brazed plate heat exchangers can be configured as one-, two- or multi-pass versions with a wide range of connection designs and locations.

The products are offered pre-configured available from stock for swift delivery. If these units do not meet the demand specification, you have the option to have a heat exchanger designed to meet your exact requirement.




Testing

The BHEs are individually leak and pressure tested to ensure first-class quality, and Alfa Laval has approvals from all major certification bodies.

Approvals

- PED
- KHK
- UL
- KIWA
- ASME



BHE's can be designed in many different ways to optimize our customers needs.

