

MODEL ⁽¹⁾	COIL CAPACITY ⁽²⁾ (Btu/h per °FTD)		COIL PHYSICAL DATA					AIRSIDE DATA					Unit Weight (lbs)	
			No. of Rows	Fins (fpi)	FaceArea (ft ²)	Surface (ft ²)	Volume (ft ³)	FanDia (inch)	Air Flow		Motors			Sound ⁽³⁾
	Wet	Frosted							(cfm)	(fpm)	Qty	(hp)		dB(A)
SCS - 163SH	2,040	1,860	6	3	5.21	353	0.83	20	3,124	600	1	1/3	64.4	449
SCS - 164SH	2,170	1,980	6	4	5.21	458	0.83	20	3,064	588	1	1/3	64.4	487
SCS - 166SH	2,400		6	6	5.21	667	0.83	20	2,948	566	1	1/3	64.4	564
SCS - 163SL		2,230	6	3	5.21	353	0.83	20	4,251	816	1	1/2	67.9	449
SCS - 164SL		2,370	6	4	5.21	458	0.83	20	4,127	792	1	1/2	67.9	487
SCS - 163MH	2,430	2,210	6	3	6.25	424	0.99	24	3,696	591	1	1/3	58.8	506
SCS - 164MH	2,570	2,340	6	4	6.25	550	0.99	24	3,601	576	1	1/3	58.8	552
SCS - 166MH	2,820		6	6	6.25	801	0.99	24	3,438	550	1	1/3	58.8	644
SCS - 163ML		2,700	6	3	6.25	424	0.99	24	5,202	832	1	1/2	62.6	506
SCS - 164ML		2,860	6	4	6.25	550	0.99	24	5,005	801	1	1/2	62.6	552
SCS - 163TH	2,880	2,610	6	3	7.29	495	1.16	24	4,409	605	1	1/3	64.9	563
SCS - 164TH	3,050	2,780	6	4	7.29	641	1.16	24	4,303	590	1	1/3	64.9	617
SCS - 166TH	3,360		6	6	7.29	934	1.16	24	4,121	565	1	1/3	64.9	724
SCS - 163TL		3,160	6	3	7.29	495	1.16	24	6,121	839	1	3/4	72.6	563
SCS - 164TL		3,370	6	4	7.29	641	1.16	24	5,946	815	1	3/4	72.6	617
SCS - 163XH	3,580	3,250	6	3	8.75	594	1.35	24	5,607	641	1	1/2	65.8	646
SCS - 164XH	3,810	3,460	6	4	8.75	769	1.35	24	5,486	627	1	1/2	65.8	710
SCS - 166XH	4,210		6	6	8.75	1121	1.35	24	5,269	602	1	1/2	65.8	839
SCS - 183XH	4,270	3,880	8	3	8.75	792	1.80	24	5,375	614	1	1/2	65.8	758
SCS - 184XH	4,510	4,100	8	4	8.75	1026	1.80	24	5,232	598	1	1/2	65.8	843
SCS - 186XH	4,850		8	6	8.75	1495	1.80	24	4,979	569	1	1/2	65.8	1016
SCS - 163XL		3,760	6	3	8.75	594	1.35	28	7,212	824	1	3/4	72.8	646
SCS - 164XL		4,000	6	4	8.75	769	1.35	28	6,992	799	1	3/4	72.8	710
SCS - 183XL		4,490	8	3	8.75	792	1.80	28	6,800	777	1	3/4	72.8	758
SCS - 184XL		4,740	8	4	8.75	1026	1.80	28	6,545	748	1	3/4	72.8	843
SCS - 263SH	4,080	3,720	6	3	10.42	707	1.50	20	6,248	600	2	1/3	67.4	848
SCS - 264SH	4,340	3,960	6	4	10.42	916	1.50	20	6,128	588	2	1/3	67.4	924
SCS - 266SH	4,800		6	6	10.42	1334	1.50	20	5,896	566	2	1/3	67.4	1078
SCS - 263SL		4,460	6	3	10.42	707	1.50	20	8,502	816	2	1/2	70.9	848