

Elevated Conveyor with Loma IC Metal Detector

Loma IC Metal Detector

- ▶ Model 925260/925929
- ▶ Aperture Size: 5-7/8 in H x 19-3/4 in L x 11-3/4 in Deep, 4-3/4 in clearance above belt
- ▶ External Dimensions: 32 in L x 11-3/4 in W x 14 in H

Conveyor

- ▶ 18 ft L Slotted belt
 - ▶ Belt Slots: 15 in W x 18 in L x 2 in H
 - ▶ Highest Point on Belt: 9 ft 3 in
 - ▶ Lowest Point on Belt: 8 in
 - ▶ Conveyor Drive: 3/4 HP 208-230/460 Volt 1725 RPM
 - ▶ Conveyor Side Rails: 12 in H x 17 in W
 - ▶ Conveyor Drive: 3/4 HP 208-230/460 Volt 1725 RPM
-
- ▶ Stainless Steel Frame

Overall Dimensions

17-1/2 in L x 38 in W x 10 ft H









