

| MODEL <sup>(1)</sup> | COIL CAPACITY <sup>(2)</sup><br>(Btu/h per °FTD) |         | COIL PHYSICAL DATA |               |                                |                               |                              | AIRSIDE DATA     |          |       |        |      | Unit<br>Weight<br>(lbs) |                      |
|----------------------|--|---------|--------------------|---------------|--------------------------------|-------------------------------|------------------------------|------------------|----------|-------|--------|------|-------------------------|----------------------|
|                      |  |         | No. of<br>Rows     | Fins<br>(fpi) | FaceArea<br>(ft <sup>2</sup> ) | Surface<br>(ft <sup>2</sup> ) | Volume<br>(ft <sup>3</sup> ) | FanDia<br>(inch) | Air Flow |       | Motors |      |                         | Sound <sup>(3)</sup> |
|                      | Wet  | Frosted |                    |               |                                |                               |                              |                  | (cfm)    | (fpm) | Qty    | (hp) |                         | dB(A)                |
| SCS - 563SH          | 10,200   | 9,300   | 6                  | 3             | 26.04                          | 1767                          | 3.51                         | 20               | 15,620   | 600   | 5      | 1/3  | 70.6                    | 2045                 |
| SCS - 564SH          | 10,850   | 9,900   | 6                  | 4             | 26.04                          | 2290                          | 3.51                         | 20               | 15,320   | 588   | 5      | 1/3  | 70.6                    | 2235                 |
| SCS - 566SH          | 12,000   |         | 6                  | 6             | 26.04                          | 3336                          | 3.51                         | 20               | 14,740   | 566   | 5      | 1/3  | 70.6                    | 2620                 |
| SCS - 563SL          |  | 11,150  | 6                  | 3             | 26.04                          | 1767                          | 3.51                         | 20               | 21,255   | 816   | 5      | 1/2  | 74.1                    | 2045                 |
| SCS - 564SL          |  | 11,860  | 6                  | 4             | 26.04                          | 2290                          | 3.51                         | 20               | 20,635   | 792   | 5      | 1/2  | 74.1                    | 2235                 |
| SCS - 563MH          | 12,150   | 11,060  | 6                  | 3             | 31.25                          | 2120                          | 4.22                         | 24               | 18,480   | 591   | 5      | 1/3  | 65.0                    | 2331                 |
| SCS - 564MH          | 12,850   | 11,720  | 6                  | 4             | 31.25                          | 2748                          | 4.22                         | 24               | 18,005   | 576   | 5      | 1/3  | 65.0                    | 2559                 |
| SCS - 566MH          | 14,100   |         | 6                  | 6             | 31.25                          | 4003                          | 4.22                         | 24               | 17,190   | 550   | 5      | 1/3  | 65.0                    | 3021                 |
| SCS - 563ML          |  | 13,510  | 6                  | 3             | 31.25                          | 2120                          | 4.22                         | 24               | 26,010   | 832   | 5      | 1/2  | 68.8                    | 2331                 |
| SCS - 564ML          |  | 14,310  | 6                  | 4             | 31.25                          | 2748                          | 4.22                         | 24               | 25,025   | 801   | 5      | 1/2  | 68.8                    | 2559                 |
| SCS - 563TH          | 14,400   | 13,090  | 6                  | 3             | 36.46                          | 2474                          | 4.92                         | 24               | 22,045   | 605   | 5      | 1/3  | 71.1                    | 2617                 |
| SCS - 564TH          | 15,250   | 13,900  | 6                  | 4             | 36.46                          | 3206                          | 4.92                         | 24               | 21,515   | 590   | 5      | 1/3  | 71.1                    | 2883                 |
| SCS - 566TH          | 16,800   |         | 6                  | 6             | 36.46                          | 4670                          | 4.92                         | 24               | 20,605   | 565   | 5      | 1/3  | 71.1                    | 3422                 |
| SCS - 563TL          |  | 15,840  | 6                  | 3             | 36.46                          | 2474                          | 4.92                         | 24               | 30,605   | 839   | 5      | 3/4  | 78.8                    | 2617                 |
| SCS - 564TL          |  | 16,860  | 6                  | 4             | 36.46                          | 3206                          | 4.92                         | 24               | 29,730   | 815   | 5      | 3/4  | 78.8                    | 2883                 |
| SCS - 563XH          | 17,900   | 16,290  | 6                  | 3             | 43.75                          | 2969                          | 5.86                         | 24               | 28,035   | 641   | 5      | 1/2  | 72.0                    | 3028                 |
| SCS - 564XH          | 19,050   | 17,340  | 6                  | 4             | 43.75                          | 3847                          | 5.86                         | 24               | 27,430   | 627   | 5      | 1/2  | 72.0                    | 3348                 |
| SCS - 566XH          | 21,050   |         | 6                  | 6             | 43.75                          | 5604                          | 5.86                         | 24               | 26,345   | 602   | 5      | 1/2  | 72.0                    | 3994                 |
| SCS - 583XH          | 21,350   | 19,410  | 8                  | 3             | 43.75                          | 3958                          | 7.81                         | 24               | 26,875   | 614   | 5      | 1/2  | 72.0                    | 3591                 |
| SCS - 584XH          | 22,550   | 20,510  | 8                  | 4             | 43.75                          | 5130                          | 7.81                         | 24               | 26,160   | 598   | 5      | 1/2  | 72.0                    | 4017                 |
| SCS - 586XH          | 24,250   |         | 8                  | 6             | 43.75                          | 7473                          | 7.81                         | 24               | 24,895   | 569   | 5      | 1/2  | 72.0                    | 4879                 |
| SCS - 563XL          |  | 18,820  | 6                  | 3             | 43.75                          | 2969                          | 5.86                         | 28               | 36,060   | 824   | 5      | 3/4  | 79.0                    | 3028                 |