

Stainless Steel Dual Paddle Blender with Screw Auger Discharge

Mfg:

Model:

Stock No. tGHFI01.

Serial No.

Stainless Steel Dual Paddle Blender with Screw Auger Discharge. Maximum capacity: 4.27 cu. ft. Minimum capacity: 2.92 cu. ft. Auger screw diameter: 5-1/2 in. dia. Auger screw housing diameter: 5-3/4 in. Auger screw length: 30 in. Baldor Industrial Motor: 5 hp, 1725 rpm, 230/460 V, 13.2/6.8 amps, 60 Hz, 3 phase. Motor Drive: no nameplate information. Inlets: (1) 2 in. dia. FPT. Outlet: (1) 5-3/4 in. dia. (4) Casters for easy positioning. Overall dimensions: 62 in. L x 19 in. W x 34 in. H.

