

1995 APV HTST Pasteurizer

Mfg: APV


Model: SR5-S

Stock No. tLXBK002.


Serial No. 30639


1995 APV HTST Pasteurizer. Model: SR5-S. S/N: 30639. W.O: 30639. Number of stainless steel plates: 121. Heat transfer surface area: approx. 120.5 sq. ft. 1994 ITT Bell & Gossett Shell and Tube Heat Exchanger, Model: 94Z79905-04, shell MAWP: 150 psi @ 375 °F, shell MDMT: -20 °F @ 150 psi, tube MAWP: 150 psi @ 375 °F, tube MDMT: -20 °F @ 150 psi. Stainless Steel Holding Tube- 5.8 Gallon. ABB Kent Taylor 4-Pen Temperature Chart Recorder, Model: Commander 1900, S/N: E/34631/8/6, 110 V. Eaton IDT PanelMate 1000, Model: 10807-015, S/N: 18-30VDC. MP Pumps Inc. Centrifugal Pump, Model: 27675, S/N: 95G 512. Baldor Industrial Motor, 1 hp, 3450 rpm, 208-230/460 V, 1.2-3/1.5 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. S-line fitting. Outlets: (1) 1-1/2 in. dia. S-line fitting (holding tube). Overall dimensions: 82 in. L x 49 in. W x 86 in. H.

APV R3BS Positive Displacement Pump and Balance Tank Skid. Model: R3BS. S/N: H-6911-94. Pumping capacity: 17.8 gpm. Maximum capacity: 36 gpm. Maximum speed: 900 rpm. Displacement: 6.40 gpm/100 rpm. Seal option: double mechanical with flushing. Reliance S-2000 Motor, 2 hp, 1725 rpm, 208-230/460-480 V, 6.4-6.4/3.2-3.4 amps, 60 Hz, 3 phase. Dodge Master XL Speed Reducer, 6.2 ratio, torque of 835 lb-in, max. input hp 3.88, final rpm: 278. (2) 13 gal tanks with 15-1/2 in dia. top covers and two 3/4 in. dia. s-line inlets. Lightnin Portable Mixer, Model: SIU05T, S/N: 95/800000, (3) 8 in. dia. propellers. Reliance Electric Motor, 1/15 hp, 1600 rpm, 115 V, 1.1 amps, 60 Hz. Stainless steel frame mounted. (4) Wheels for easy maneuverability. Inlets: (3) 1 in. dia. tank infeeds. Outlets: (1) 1 in. dia s-line fitting. Overall dimensions: 48 in. L x 38 1/2 in. W x 69 in. H.









APV R3BS Positive Displacement Pump and Balance Tank Skid

Mfg: APV

Model: R3BS

Stock No. tLXBK003.

Serial No. H-6911-94

APV R3BS Positive Displacement Pump and Balance Tank Skid. Model: R3BS. S/N: H-6911-94. Pumping capacity: 17.8 gpm. Maximum capacity: 36 gpm. Maximum speed: 900 rpm. Displacement: 6.40 gpm/100 rpm. Seal option: double mechanical with flushing. Reliance S-2000 Motor, 2 hp, 1725 rpm, 208-230/460-480 V, 6.4-6.4/3.2-3.4 amps, 60 Hz, 3 phase. Dodge Master XL Speed Reducer, 6.2 ratio, torque of 835 lb-in, max. input hp 3.88, final rpm: 278. (2) 13 gal tanks with 15-1/2 in dia. top covers and two 3/4 in. dia. s-line inlets. Lightning Portable Mixer, Model: SIU05T, S/N: 95/800000, (3) 8 in. dia. propellers. Reliance Electric Motor, 1/15 hp, 1600 rpm, 115 V, 1.1 amps, 60 Hz. Stainless steel frame mounted. (4) Wheels for easy maneuverability. Inlets: (3) 1 in. dia. tank infeeds. Outlets: (1) 1 in. dia s-line fitting. Overall dimensions: 48 in. L x 38 1/2 in. W x 69 in. H.

I/A Series Magnetic Flow Transmitter, Model: IMT20-5A16FGZ-T, supply power: 120 Vac, 30 VA max, 4-20 milliamps (current out), 50/60 Hz. Foxboro 8000A Series Magnetic Flowtube, MAWP 450 psi @ 200 °F, MAWP 150 psi @ 350 °F. Woods E-TRAC AC Inverter- 2 HP, input: 2.8 KVA, 230 V, 12.4 amps, 50/60 Hz, single phase, output (cont.): 3.0 KVA, 230 V, 7.5 amps, 3 phase, 7.5 amps.



